

# SYSTIMAX® UD Fiber Panel Announcement: New Product

## Global Communication

CommScope® announces the release of the SYSTIMAX® Ultra Density (UD) Fiber Solutions. The SYSTIMAX® UD solution is built to support ultra, high density data center applications based on LC and MPO connectivity. The solution combines high density with manageability and ease of making moves, additions and changes. At the heart of the SYSTIMAX® UD solution are the 2U and 4U UD fiber panels. Each of the panels accepts InstaPATCH® 360 Modules or MPO connector pass-through panels, and can be upgraded to add AIM (Automated Infrastructure Management) based intelligence.



- Panel design optimized for pre-term, making moves/adds/changes easier while minimizing network downtime
- Split tray design scales up density quickly and easily without disrupting live channels
- Tool-less install of rear trunk cables significantly reduces trunk installation time
- Innovative, flexible labeling solutions for easy port identification
- Large, translucent window provides clear view of the patching field
- Solid robust 2U/4U fiber panels scalable to 288 duplex LC ports or 192 MPO ports
- Supports imVision AIM solution with addition of iPatch upgrade kits

### Ordering Information:

Please visit eCatalog for product specs: <http://www.commscope.com/Product-Catalog/Enterprise/>

Part Number	Product Code	Descriptions
760227306	UD-2U	SYSTIMAX® UD 2U sliding fiber panel, accepts (12) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 144 duplex LC ports or up to 96 MPO ports
760227314	UD-4U	SYSTIMAX® UD 4U sliding fiber panel, accepts (24) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 288 duplex LC ports or up to 192 MPO ports
760218461	UD-2U-FX	SYSTIMAX® UD 2U fixed fiber panel, accepts (12) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 144 duplex LC ports or up to 96 MPO ports

Part Number	Product Code	Descriptions
760218479	UD-4U-FX	SYSTIMAX® UD 4U fixed fiber panel, accepts (24) InstaPATCH® 360 modules or MPO pass-thru panels, providing up to 288 duplex LC ports or up to 192 MPO ports

### SYSTIMAX® UD Panels with imVision AIM

Part Number	Product Code	Descriptions
760236362	UD-iP-2U-96-MPO-DP-SD	UD iPATCH 2U 96-MPO Distribution Panel, Sliding Shelf
760236363	UD-iP-2U-288F-LC-DM-WB-SD	UD iPATCH 2U 288F-LC Distribution Module, LazrSPEED WideBand, Sliding Shelf
760236364	UD-iP-2U-288F-LC-DM-LS-SD	UD iPATCH 2U 288F-LC Distribution Module, LazrSPEED, Sliding Shelf
760236365	UD-iP-2U-288F-LC-DM-TS-SD	UD iPATCH 2U 288F-LC Distribution Module, Tera Speed, Sliding Shelf
760236366	UD-iP-2U-288F-LC-DM08-ULL-WB-SD	UD iPATCH 2U 288F-LC Distribution MPO08 ULL Module, LazrSPEED WideBand, Sliding Shelf
760236367	UD-iP-2U-288F-LC-DM08-ULL-LS-SD	UD iPATCH 2U 288F-LC Distribution MPO08 ULL Module, LazrSPEED, Sliding Shelf
760236368	UD-iP-2U-288F-LC-DM12-ULL-WB-SD	UD iPATCH 2U 288F-LC Distribution MPO12 ULL Module, LazrSPEED WideBand, Sliding Shelf
760236369	UD-iP-2U-288F-LC-DM12-ULL-LS-SD	UD iPATCH 2U 288F-LC Distribution MPO12 ULL Module, LazrSPEED, Sliding Shelf
760236370	UD-iP-2U-288F-LC-DM24-ULL-WB-SD	UD iPATCH 2U 288F-LC Distribution MPO24 ULL Module, LazrSPEED WideBand, Sliding Shelf
760236371	UD-iP-2U-288F-LC-DM24-ULL-LS-SD	UD iPATCH 2U 288F-LC Distribution MPO24 ULL Module, LazrSPEED, Sliding Shelf