760188334 | 360G2-iP-1U-96F-LC-DM-OS-SD



SYSTIMAX 360™ iPatch® InstaPATCH 1U 96F-LC Distribution Module, OptiSPEED, Sliding Panel

OBSOLETE

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber splice panel

Product Brand SYSTIMAX 360™ | iPatch®

General Specifications

Color Black

Intelligence Type iPatch® enabled

Interface, front LC

Rack Units 1

Shelf Movement Sliding **Total Ports, quantity** 48

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 478.79 mm | 18.85 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

Optical Specifications

COMMSCOPE®

760188334 | 360G2-iP-1U-96F-LC-DM-OS-SD

Fiber Mode Multimode

Environmental Specifications

Operating Temperature $-5 \, ^{\circ}\text{C} \text{ to } +50 \, ^{\circ}\text{C} \text{ (+23 } ^{\circ}\text{F to } +122 \, ^{\circ}\text{F)}$

Storage Temperature $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard Austel | CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 2.948 kg | 6.5 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

