# 760188342 | 360G2-iP-1U-96F-LC-DM-LS-UHD



SYSTIMAX 360™ iPatch® InstaPATCH 1U 96F-LC Distribution Module, LazrSPEED, UHD Panel

#### **OBSOLETE**

#### Replaced By:

760168435 SYSTIMAX 360™ iPatch® InstaPATCH 1U 96F-LC Distribution Module, LazrSPEED, Sliding 360G2-iP-1U-96F-LC-DM-LS-SD Panel

760218396

HD-iP-1U-48F-LC-DM-LS-SD

HD iPATCH 1U 48F-LC Distribution Module, LazrSPEED, Sliding Panel

### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber splice panel

Product Brand SYSTIMAX 360™ | iPatch®

## General Specifications

**Color** Black

Intelligence Type iPatch® enabled

Interface, front LC/UPC

Rack Units 1

Shelf Movement Fixed

Total Ports, quantity 48

### **Dimensions**

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 492.76 mm | 19.4 in

Page 1 of 2



# 760188342 | 360G2-iP-1U-96F-LC-DM-LS-UHD

## Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

**Optical Specifications** 

**Fiber Mode** Multimode

## **Environmental Specifications**

**Operating Temperature**  $-5 \, ^{\circ}\text{C} \text{ to } +50 \, ^{\circ}\text{C} \text{ (+23 } ^{\circ}\text{F to } +122 \, ^{\circ}\text{F)}$ 

**Storage Temperature**  $-40~^{\circ}\text{C}$  to  $+70~^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158~^{\circ}\text{F}$ )

**Relative Humidity** Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard Austel | CE | CSA | UL

Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

