



SYSTIMAX 360™ iPatch® InstaPATCH 2U 192F-LC Distribution Module, LazrSPEED, Sliding Panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	SYSTIMAX 360™ iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	LC/UPC
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	96

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	478.79 mm 18.85 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
---------------	--

Optical Specifications

Fiber Mode	Multimode
------------	-----------

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	Austel CE CSA UL

Packaging and Weights

Packaging quantity	1
Weight, net	5.897 kg 13 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

