760231456 | SD-2U



Standard Density 2U sliding Panel, accepts (6) LGX/1000 style splice cassettes, modules or panels, providing up to 72 duplex LC ports

OBSOLETE

This product was discontinued on: October 31, 2022

Replaced By:

760251045 EPX 2U sliding panel, accepts (6) LGX/PNL style splice cassettes, modules or panels, providing up to

EPX-2U-PNL-ENC 72 duplex LC ports

Product Classification

Portfolio CommScope®

Product Type Fiber patch panel

Product Series SD

General Specifications

Application Accepts six LGX/1000 footprint panels/cassettes

Color Black
Interface, front Unloaded

Rack Units 2

Shelf Movement Sliding

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 474.98 mm | 18.7 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC) | Steel

Page 1 of 2



760231456 | SD-2U

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 7.847 kg | 17.3 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



