760206540 | 360DMis-24LC-SM



G2 LL Singlemode MPO 12 distribution module, 24 LC to 2x12f MPO's pinned, internal shutters

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber module

Product Brand InstaPATCH® 360

Product Series G2

General Specifications

FunctionalityBreakoutColor, frontBlueColor, rearGrayInterface, frontLC/UPCInterface, rearMPO

Interface Feature, rear Key up/up | Pinned

Polarity Method B
Shuttered Yes
Total Fibers, quantity 24

Dimensions

 Height
 25.51 mm | 1.004 in

 Width
 95.91 mm | 3.776 in

 Depth
 119.69 mm | 4.712 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Insertion Loss, maximum 1.05 dB

COMMSCOPE®

760206540 | 360DMis-24LC-SM

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.109 kg | 0.24 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



