TFAH-ES70/80-37



 ${\rm ION} \ensuremath{\mathbb{R}}$ -B Series High Power Remote Unit for LMR 700 and LMR 800 Band High Power Applications

Product Classification	
Product Type	Remote unit
Product Brand	ION®-B
General Specifications	
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	High
Electrical Specifications	
Impedance	50 ohm
License Band	LMR 700 LMR 800
Voltage Range	-60 to -36 Vdc
Electrical Specifications, Rx (Uplink)	
Operating Frequency Band	788 – 806 MHz (LMR 700) 806 – 824 MHz (LMR 800)
Electrical Specifications, Tx (Downlink)	
Operating Frequency Band	758 – 775 MHz (LMR 700) 851 – 869 MHz (LMR 800)

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Page 1 of 1

