

	-	8	7 6		
	ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
	1	IC0601	6' ICE SHIELD SUPPORT BRACKET	2	38.89 LBS
	2	WB-CY210	SAFETY GRATING 24" X 10'	3	111.00 LBS
D	3	GUB-4355	1/2" X 3-5/8" X 5" GALV U-BOLT	8	0.57 LBS
	4	GJB0380	8" GALV J-BOLT KIT	12	0.25 LBS
	5	MT-387	SQUARE WASHER, 1-1/2" X 1-5/8" W/ 7/16" HOLE	12	0.12 LBS
	6	GWL-03	3/8" GALV LOCK WASHER	12	0.01 LBS
	7	GN-03	3/8" GALV HEX NUT	12	0.04 LBS
	8	MF126.01	BASE SHOE	4	69.59 LBS
	9	MT-287	3/4" x 7" WEDGE ANCHOR	8	0.72 LBS



В

А



8			1	
EM PART NO.		D)/	DATE	_
1 IC0601	O ICE SHIELD SUPPORT DRACKET Z 50.09 LDS	BY ACG	DATE 03/29/07	-
2 WB-CY210	D SAFETY GRATING 24" X 10' 3 111.00 LBS		L	-
3 GUB-4355				
4 GJB0380	8" GALV J-BOLT KIT 12 0.25 LBS			
5 MT-387	SQUARE WASHER, 1-1/2" X 1-5/8" W/ 7/16" HOLE 12 0.12 LBS			
6 GWL-03	3/8" GALV LOCK WASHER 12 0.01 LBS			D
7 GN-03	3/8" GALV HEX NUT 12 0.04 LBS			
8 MF126.01				
9 MT-287	3/4" x 7" WEDGE ANCHOR 8 0.72 LBS			
				C
		<b>B</b>		В
	These drawings and specifications, are the proprietary			A
	These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific action writing by Andrew Corporation.			_
	ALL DIMENSIONS ARE IN INCHES U.O.S. TP NTS 6' X 10' ICE CANOPY W/ BASE SHOE LEGS			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:Date:Date:Definition $X = \pm .06$ ANGLES $\pm 2'$ 03/29/07A36, A53, A568ASSEMBLY DRAWING			]
	$.XX = \pm .03 \qquad \text{FRACTIONS} \qquad \pm 1/32 \qquad \qquad \underbrace{\text{REVISIONS}}_{\text{REVISIONS}} \qquad \underbrace{\text{REVISIONS}} \qquad \underbrace{\text{REVISIONS}} \qquad \underbrace{\text{REVISIONS}} \qquad \text$			-
NOTES:	REMOVE BURRS AND BREAK EDGES .005		RK, IL. 60462	
I. AL	L METRIC DIMENSIONS ARE IN BRACKETS.	S.A.		
8			1	