# NPC06UVDB



#### NETCONNECT® Cat 6 U/UTP RJ45 Patch Cord, Non-Plenum

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- ٠ Colored pull latch tabs are available for easier plug release handling from the modular jack

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   Latin America
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Product Series	NPC
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices
General Specifications	

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Black   Blue   Green   Orange   Red   Slate   White   Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4   ISO/IEC 11801 Class E
Wiring	T568B
Dimensions	
Cable Assembly Length Range (m)	1 – 30

Page 1 of 3


©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: November 14, 2022



## NPC06UVDB

Cable Assembly Length Range (ft)	1 – 100
Cable Assembly Length Range (cm)	15 – 999
Cable Assembly Length Range (in)	6 – 999
Diameter Over Jacket	5.97 mm   0.235 in
Compatible Conductor Gauge, stranded	24 AWG

## Ordering Tree



## Material Specifications

Insulation Material	Polyethylene
Material Type	PVC
Mechanical Specifications	
Plug Insertion Life, minimum	750 times
Environmental Specifications	
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing
Environmental Space	Non-plenum

**Flammability Rating** 

Safety Standard

СМ UL 1863

## Packaging and Weights

Page 2 of 3

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: November 14, 2022



# NPC06UVDB

#### Packaging quantity

1

#### Regulatory Compliance/Certifications

#### Classification

Agency RCM

Compliant to electrical safety & telecommunications requirements



Included Products

2843020-3<br/>MP-6AU-Boot-59-1-Integrated Boot and Pair Manager for MP-6AU, size 59, transparent6-2843007-1<br/>MP-6AU-Plug-A-1-Modular Plug, Category 6A/6, Unshielded, Cond Insulation OD - 0.99mm, 100<br/>pcs

Page 3 of 3

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: November 14, 2022

