## 9-554720-3 | MP-88U-F-1-TW



Modular Plug, 8P/8C, unshielded, flat oval, 8-position, category 5, Taiwan, 100 pcs

#### **Product Classification**

Regional Availability Asia

 Portfolio
 CommScope®

 Product Type
 Modular plug

General Specifications

ANSI/TIA Category 5

 Cable Type
 Flat oval, unshielded

 Conductor Type
 Solid | Stranded

InterfaceRJ45Positions/Loaded Contacts8/8Termination TypeIDC

#### **Dimensions**

Compatible Cable Diameter, maximum8.89 mm0.35 inCompatible Cable Diameter, minimum2.54 mm0.1 inCompatible Insulated Conductor Diameter, maximum0.99 mm0.039 inCompatible Insulated Conductor Diameter, minimum0.86 mm0.034 in

Contact Plating Thickness1.27 μmCompatible Conductor Gauge, solid26-24 AWGCompatible Conductor Gauge, stranded26-24 AWG

### **Electrical Specifications**

 Current Rating, maximum
 0.75 A

 Insulation Resistance, minimum
 500 mOhm

COMMSCOPE®

# 9-554720-3 | MP-88U-F-1-TW

Safety Voltage Rating 150 Vac

Material Specifications

Contact Base Material Phosphor Bronze

Contact Plating Material Gold

Material Type Glass filled polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

**Environmental Specifications** 

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Relative Humidity** Up to 93%, non-condensing

Flammability Rating UL 94 V-2
Safety Standard UL 1863

Packaging and Weights

Packaging quantity 100

Packaging Type Bag | Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

