

# 243095-11



Stainless Steel Hardware Kit for 1/2 in or 7/8 in Block style hangers, includes M10 bolts and hardware, 101.09 mm (3.98 in) length

## Product Classification

Product Type	Hardware kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

## General Specifications

Thread Size	M10
-------------	-----

## Dimensions

Maximum Stack Height	1
Length	101.092 mm   3.98 in
Nominal Size	1/2 in   7/8 in

## Material Specifications

Material Type	Stainless steel 304
---------------	---------------------

## Packaging and Weights

Height, packed	50.8 mm   2 in
Width, packed	20.32 mm   0.8 in
Length, packed	20.32 mm   0.8 in
Included	Forty flat washers   Forty lock washers   Ten M10 threaded rods   Twenty hex nuts
Packaging quantity	10
Weight, gross	0.109 kg   0.24 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power