## CB-12-50



Cable Banding, Bulk, 1/2 in x 50 ft Reel (uses CB-LH-25 Locking Heads - not incl)

#### **Product Classification**

Product Type Banding

Ordering Note CommScope® standard product (Global)

#### General Specifications

Adapter Type Adapter

Color Black

**Mounting** Round member

#### **Dimensions**

 Width
 12.7 mm | 0.5 in

 Length
 15.24 m | 50 ft

 Material Thickness
 1.524 mm | 0.06 in

#### Material Specifications

Material Type Heat-stabilized weather resistant acetal

#### Mechanical Specifications

**Tensile Force** 1,112.055 N | 250 lbf

#### **Environmental Specifications**

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Operating Temperature  $-65 \,^{\circ}\text{C}$  to  $+90 \,^{\circ}\text{C}$  (-85  $^{\circ}\text{F}$  to  $+194 \,^{\circ}\text{F}$ )

## Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

**COMMSCOPE®** 

# CB-12-50

CHINA-ROHS Below maximum concentration value

CSA Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





