
ALGLGUCCM

Base Product



Ultra Low Loss ULL TeraSPEED® LC/UPC to Unconnectorized Ruggedized fanout Cable, 144-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

in meters | Minimum length may vary based on cable configuration

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East/Africa North America	
Portfolio	CommScope®	
Product Type	Ruggedized fanout	
Product Brand	SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be	

General Specifications

Color, boot A	Blue
Color, connector A	Green
Color, boot B	Blue
Color, connector B	Blue
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	LC/APC
Interface Feature, connector A	ULL
Interface, Connector B	Unterminated
Interface Feature, connector B	ULL
Jacket Color	Yellow
Fibers per Subunit, quantity	12
Total Fibers, quantity	144
Dimensions	
Cable Assembly Length Range (m)	3 – 305

Cable Assembly Length Range (ft)	10 – 999

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024



ALGLGUCCM

Ordering Tree

BASE CODE - J					•
Jacket Color			Breakout Length / Option	L	ength
	Yellow	Е	24 inch breakout, no gland		
		F	24 inch breakout, with gland		
		1	33/60 inch breakout, no gland		
		2	33/60 inch breakout, with gland		
3		3	33/60 inch breakout, with pulling grip	ļ	JOM
		н	48 inch breakout, no gland	F	Feet
		J	48 inch breakout, with gland	М	Meter
		L	72 inch breakout, no gland		
		М	72 inch breakout, with gland		
		S	36 inch breakout, no gland		
		U	36 inch breakout, with gland		
		V	60 inch breakout, no gland		
		W	60 inch breakout, with pulling grip		

Optical Specifications

Fiber Mode

Fiber Type

Singlemode G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
Environmental Space	Indoor Plenum

Regulatory Compliance/Certifications

Agency	Classi
ANATEL	Comp

ification

Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

COMMSCOPE°

ALGLGUCCM



Included Products

760242061 P-144-MP-8G-F12YL/20T Fiber Indoor Cable, Plenum MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2/B2, Gel-free, Feet jacket marking, Yellow jacket color

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

