1711163-1 | CS54Z3 WHT C7 4/23 F/FTP RL 500M



CS54Z3 Category 7 F/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

Product Classification

Diameter Over Jacket, nominal

Electrical Specifications

Characteristic Impedance Tolerance

Conductor Gauge, singles

Characteristic Impedance

Coupling Attenuation

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair cable
General Specifications	
ANSI/TIA Category	7
Cable Component Type	Horizontal
Cable Type	F/FTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Pairs, quantity	4
Transmission Standards	CENELEC EN 50288-4-1 IEC 61156-5 Cat 7 ISO/IEC 11801 Class F
Dimensions	
Cable Length	500 m 1,640.42 ft
Diameter Over Insulated Conductor	1.501 mm 0.059 in

7.399 mm | 0.291 in

23 AWG

100 ohm

±15 ohm

Type Ib

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 23, 2024



1711163-1 | CS54Z3 WHT C7 4/23 F/FTP RL 500M

29.6 mm | 1.165 in

dc Resistance, maximum	9.38 ohms/100 m 2.859 ohms/100 ft
Nominal Velocity of Propagation (NVP)	78 %
Operating Frequency, maximum	600 MHz
Operating Voltage, maximum	80 V
Segregation Class	d
Transfer Impedance	Grade 2
Material Specifications	
Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Zero Halogen (LSZH)
Mechanical Specifications	

Minimum Bend Radius, multiple Bends

Environmental Specifications

Installation temperature	0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2
EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	al
Flame Test Method	IEC 60332-3
Dackaging and Mojepts	

Packaging and Weights

Cable weight	51.996 kg/km 34.94 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 23, 2024





UK-ROHS

Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 23, 2024

