



FTP-PC6-GYx

Uniprise® Category 6 Foiled Twisted Pair (FTP) Modular Patch Cord

The Uniprise FTP Modular Patch Cord (FTP-PC6-GYx) consists of high quality components designed to assure high performance in Category 6 applications. This product meets the Category 6 specifications as specified in ANSI/TIA/EIA 568-B.2-1, IEC 60603-7-5 and ISO/IEC 11801.

The Uniprise FTP Modular Patch Cord is designed to mate with FTP-J6 information outlets to minimize signal reflections and significantly improve performance.

When installed with a Uniprise FTP-J6 Information Outlet, FTP Modular Patch Panel and Category 6 Foiled Twisted Pair Cables, the result is an end-to-end channel performance and superior electromagnetic compatibility (EMC) performance in high external noise environments.

FEATURES & BENEFITS:

- Enhanced plug design, improved 24-gauge (0.511 mm) cordage and a unique manufacturing process assures extremely high electrical performance with low variability
- Improved anti-snag feature provides maximum protection from snagging during moves, adds and changes
- Available in gray solid conductor cordage
- UL listed
- Can support high bandwidth applications including IEEE 802.3ab 1000BASE-T (Gigabit Ethernet)
- Qualifies for a Uniprise FTP Solutions 20-Year Extended Product Warranty when included in a certified Uniprise FTP channel

PHYSICAL SPECIFICATIONS:

Operating Temperature Range:	-10 to 60 °C (14 to 140 °F)
Contact Stability:	20 mΩ max. change
Insertion Life:	750 insertions
Contact Plating:	1.27 μm Gold over 2.540 μm Nickel

Ordering Information

Catalog Number	Packaging	Color
FTP-PC6-GY3	1/Pkg	Gray
FTP-PC6-GY5	1/Pkg	Gray
FTP-PC6-GY7	1/Pkg	Gray
FTP-PC6-GY9	1/Pkg	Gray
FTP-PC6-GY15	1/Pkg	Gray
FTP-PC6-GY25	1/Pkg	Gray



© 2008 CommScope, Inc. All rights reserved.

Visit our Web site at www.commscope.com or contact your local CommScope representative or BusinessPartner for more information. All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.

This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to Uniprise products or services.