1435831 | FD3-AG432J00JCBP2-P



FDH 3000 Fiber Distribution Medium Pole Mount Cabinet, 432F, SC /APC, no splitters, dielectric loose tube, 100 ft, 24F

Product Classification

Material Type

Regional Availability	North America	
Product Type	Fiber distribution hub	
Product Series	FDH 3000	
General Specifications		
Access	Front	
Cable Type	Dielectric - Loose Tube	
Color	Putty white	
Distribution Cables, quantity	2	
Distribution Ports, quantity	432	
Fibers per Distribution Cable, quantity	216	
Fibers per Feeder Cable, quantity	24	
Interface, Input	SC	
Interface Feature, Input	APC	
Mounting	Pole	
Splitter Slots, quantity	24	
Dimensions		
Height	914 mm 35.984 in	
Width	686 mm 27.008 in	
Depth	457 mm 17.992 in	
Cable Length	30.48 m 100 ft	
Enclosure Size	Medium	
Material Specifications		
Finish	Powder coated	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 17, 2023

Steel



1435831 | FD3-AG432J00JCBP2-P

Environmental Specifications

Environmental Space

Aerial

Packaging and Weights

Packaging quantity

Packaging Type

Pallet

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 17, 2023

