F1-PNMMU-8

FSJ1-50A Jumper with interface types N Male and MINI UHF MALE,

Product Classification

Product Type		SureFlex® standard	I
Product Brand		HELIAX®	
Product Series		FSJ1-50A	
General Specifications			
Attachment, Connector A		Factory attached	
Attachment, Connector B		Factory attached	
Body Style, Connector A		Straight	
Body Style, Connector B		Straight	
Interface, Connector A		N Male	
Interface, Connector B		Mini UHF Male	
Specification Sheet Revision Level		А	
Dimensions			
Length		2.438 m 7.999 ft	
Nominal Size		1/4 in	
VSWR/Return Loss			
Frequency Band	VSWR		Return Loss (dB)

1.288

18

Jumper Assembly Sample Label

10-400 MHz

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 19, 2024



F1-PNMMU-8



Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Agency

Designed, manufactured and/or distributed under this quality management system

Included Products

 F1MU
 Mini UHF Male for 1/4 in FSJ1-50A cable

 FSJ1-50A
 FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 19, 2024

