

# F1-PNMNM-M6-HF

---

FSJ1-50A Jumper with interface types N Male and N Male, 0.6M



## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	FSJ1-50A

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	0.6 m   1.969 ft
<b>Nominal Size</b>	1/4 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
10-18000 MHz	1.58	13

## Jumper Assembly Sample Label

# F1-PNMNM-M6-HF

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition