

PB-G3T-2



Tapered Pipe Frame Stand-Off Bracket, 36 in, for 2 in to 5 in OD legs

Product Classification

Product Type Stand-off mount

General Specifications

Mounting Legs, 50.8–127 mm (2–5 in) OD
Note Four 72 in x 8 in panel antennas per sector
Tower Taper Tapered

Dimensions

Height 1,447.8 mm | 57 in
Width 254 mm | 10 in
Length 838.2 mm | 33 in
Mounting Diameter, maximum 127 mm | 5 in
Mounting Diameter, minimum 50.8 mm | 2 in
Stand-off Distance 914.4 mm | 36 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC
Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Clamps | Stand-off

PB-G3T-2

Packaging quantity 1
Weight, net 62.6 kg | 138.009 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code