

Standard Density Fiber Optic Panels & Splice Cassettes: New Product

Global Communication

CommScope® announces the release of Standard Density (SD) Fiber Optic Panels and Splice Cassettes. The SD panel comes in a variety of sizes, with fixed or sliding trays, and accepts ReadyPATCH MPO-LC modules or SD splice cassettes making it both a cost-effective and flexible solution for the data center and telecom closet.

SD splice cassettes are designed for individual pigtailed, each pre-loaded and pre-routed for quick fusion splicing. These splice cassettes provide a protective space for fusion splicing, patching and storing fiber optic cables.

- Modular design utilizing LGX footprint offers pay-and-you-grow flexibility
- Robust offering of pre-terminated, field term or splicing cassettes
- Factory-connectorized pigtailed reduces installation time
- Scalable up to 24 fibers per module
- Simplifies moves, adds and changes



Ordering Information:

Please visit eCatalog for product specs: <http://www.commscope.com/Product-Catalog/Enterprise/>

CommScope® SD Panels

| Part Number | Product Code | Description |
|-------------|--------------|---|
| 760231449 | SD-1U | SD 1U sliding fiber panel, accepts (3) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 36 duplex LC ports or up to 24 MPO ports |
| 760231456 | SD-2U | SD 2U sliding fiber panel, accepts (6) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 72 duplex LC ports or up to 48 MPO ports |

| Part Number | Product Code | Description |
|-------------|--------------|---|
| 760231464 | SD-4U | SD 4U sliding fiber panel, accepts (12) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 144 duplex LC ports or up to 96 MPO ports |
| 760231472 | SD-1U-FX | SD 1U fixed fiber panel, accepts (3) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 36 duplex LC ports or up to 24 MPO ports |
| 760231480 | SD-2U-FX | SD 2U fixed fiber panel, accepts (6) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 72 duplex LC ports or up to 48 MPO ports |
| 760231498 | SD-4U-FX | SD 4U fixed fiber panel, accepts (12) SD splice cassettes or ReadyPATCH MPO-LC modules, providing up to 144 duplex LC ports or up to 96 MPO ports |

SD Splice Cassettes

| Part Number | Product Code | Description |
|-------------|-----------------|---|
| 760221739 | PNL-CS-12LCX-PT | SD SPLICING CASSETTE 12LC LazrSPEED, 900µm |
| 760221747 | PNL-CS-12LCW-PT | SD SPLICING CASSETTE 12LC TeraSPEED, 900µm |
| 760221697 | PNL-CS-24LCX-PT | SD SPLICING CASSETTE 24LC LazrSPEED, 900µm |
| 760221705 | PNL-CS-24LCW-PT | SD SPLICING CASSETTE 24LC TeraSPEED, 900µm |
| 760221770 | PNL-CS-12SCX-PT | SD SPLICING CASSETTE 12SC LazrSPEED, 900µm |
| 760221788 | PNL-CS-12SCW-PT | SD SPLICING CASSETTE 12SC TeraSPEED, 900µm |
| 760236500 | PNL-CS-12LCX | SD SPLICING CASSETTE 12LC LazrSPEED, no pigtail |
| 760236501 | PNL-CS-12LCW | SD SPLICING CASSETTE 12LC TeraSPEED, no pigtail |
| 760236502 | PNL-CS-12LAW | SD SPLICING CASSETTE 12LC APC TeraSPEED, no pigtail |
| 760236503 | PNL-CS-24LCX | SD SPLICING CASSETTE 24LC LazrSPEED, no pigtail |
| 760236504 | PNL-CS-24LCW | SD SPLICING CASSETTE 24LC TeraSPEED, no pigtail |
| 760236505 | PNL-CS-24LAW | SD SPLICING CASSETTE 24LC APC TeraSPEED, no pigtail |
| 760236506 | PNL-CS-12SCX | SD SPLICING CASSETTE 12SC LazrSPEED, no pigtail |
| 760236507 | PNL-CS-12SCW | SD SPLICING CASSETTE 12SC TeraSPEED, no pigtail |
| 760236508 | PNL-CS-12SAW | SD SPLICING CASSETTE 12SC APC TeraSPEED, no pigtail |