

Powered Fiber Cable Ordering Options: New Product

The Indoor/Outdoor (Riser/LSZH) rated Powered Fiber Cable family is becoming more flexible to order. Previously only three length options were offered – 1km, 2km, and 4km lengths. New ordering part numbers have been created which now allow down to a 500 meter minimum order quantity, and freedom to place orders in various cut lengths similarly to how we currently offer for other bulk cable types up to a maximum of 8000 meters. This will simplify the ordering process and allow more flexibility. This change follows the Outdoor only rated cable ordering improvement which was announced in April. For example, “PFC-S02L12” now replaces these three part numbers:



- PFC-S02L12-1000M (restricted to only 1000 meter length)
- PFC-S02L12-2000M (restricted to only 2000 meter length)
- PFC-S02L12-4000M (restricted to only 4000 meter length)

Ordering Information:

Please visit eCatalog. Click Hybrid Cables

<http://www.commscope.com/poweredorfiber/>

The 10 new part numbers are now available as follows:

eCatalog Number	Description
PFC-S02L12	Powered Fiber Cable, Singlemode, 2 Fibers, Indoor/Outdoor, 12AWG
PFC-S02L16	Powered Fiber Cable, Singlemode, 2 Fibers, Indoor/Outdoor, 16AWG
PFC-S04L12	Powered Fiber Cable, Singlemode, 4 Fibers, Indoor/Outdoor, 12AWG
PFC-S04L16	Powered Fiber Cable, Singlemode, 4 Fibers, Indoor/Outdoor, 16AWG
PFC-S12L12	Powered Fiber Cable, Singlemode, 12 Fibers, Indoor/Outdoor, 12AWG
PFC-S12L16	Powered Fiber Cable, Singlemode, 12 Fibers, Indoor/Outdoor, 16AWG
PFC-302L12	Powered Fiber Cable, OM3, 2 Fibers, Indoor/Outdoor, 12AWG
PFC-302L16	Powered Fiber Cable, OM3, 2 Fibers, Indoor/Outdoor, 16AWG
PFC-304L12	Powered Fiber Cable, OM3, 4 Fibers, Indoor/Outdoor, 12AWG
PFC-304L16	Powered Fiber Cable, OM3, 4 Fibers, Indoor/Outdoor, 16AWG