

ValuDAS™ Coupler and Splitter for 698-2700 MHz Bands: New Product



CommScope announces ValuDAS™ couplers and splitters with extended frequency bands from 698 to 2700 MHz are now available globally.

- Frequency bands support 698 to 2700 MHz
- Excellent low PIM -155 dBc @ 2x43 dBm
- Low VSWR
- Application: Indoor
- Available in 4.3-10 type

Ordering Information:

Please visit the eCatalog with the links provided below.

New Model Number	Description
VD-C6-CPUSE-43-A	6 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C8-CPUSE-43-A	8 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C10-CPUSE-43-A	10 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C13-CPUSE-43-A	13 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C15-CPUSE-43-A	15 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C20-CPUSE-43-A	20 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-C30-CPUSE-43-A	30 dB, Air Directional Coupler, 698-2700, 4.3-10
VD-H2X2-CPUSE-43-A	3 dB, Hybrid Coupler, 698-2700, 4.3-10
VD-S2-CPUSE-H-43	2-way High Power Splitter, 698-2700, 4.3-10
VD-S3-CPUSE-H-43	3-way High Power Splitter, 698-2700, 4.3-10
VD-S4-CPUSE-H-43	4-way High Power Splitter, 698-2700, 4.3-10