

Enhancements to the Pre-Term Fiber Quick-Turn Program

North America Communication

The Quick-Turn Fiber program is designed to meet the needs of customers who have immediate requirements for fiber jumpers, MPO arrays and trunks. The Quick-Turn Fiber program is intended to supplement the current pre-term fiber provisioning process. This is a service provided to CommScope customers to address last minute pre-term fiber requirements, as well as fiber pre-term assemblies required to accommodate moves, adds, and changes.

- Place an order
 - Orders are placed from distributor via fax at **1-877-Qik-Cord (1-877-745-2673)** or email at quickturn@commscope.com
 - Maximum order quantity is **70 fiber jumpers and 20 trunks or arrays per order.**
 - Targeted to ship max order quantities within 2-3 days after customer submits the Quick-Turn order; lead time may vary based on availability.
 - For additional quantities, please call Customer Service. Lead time subject to availability.
- Pricing
 - Quick-Turn fiber orders qualify for the same project pricing discount.
- Shipping
 - **Customer pays for shipping charges.** Actual shipping time depends on the shipping option selected by the customer. Clear shipping instructions, including: ship to address, shipping options, and account number (FedEx, UPS, Etc.), must be included in the purchase order.

Product Sets Qualified for Quick-Turn

Patch Cords

- OM4 1.6mm Duplex (LC-LC), Riser, Aqua
- OM4 1.6mm Duplex (LC-LC), Plenum, Aqua
- Singlemode 1.6mm Duplex (LC-LC), Riser, Yellow



MPO Array Patch Cords or Array Fanouts

- OM3 12-fiber Array Patch Cord (MPO-MPO), Plenum, Aqua
- OM4 12-fiber Array Patch Cord (MPO-MPO), Plenum, Aqua
- OM4 12-fiber QSFP Array Fanout (MPO-8LC), Plenum, Aqua, BO Length = 12 in., 24in., 48 in.
- OM3 12-fiber Array Fanout (MPO-12LC), Plenum, Aqua, BO Length = 12 in., 24 in., 48 in.
- OM4 12-fiber Array Fanout (MPO-12LC), Plenum, Aqua, BO Length = 12 in., 24 in., 48 in.



Trunks

- OM3 12-fiber/24-fiber, Plenum, Aqua
- OM4 12-fiber/24-fiber/48-fiber/96-fiber/144-fiber, Plenum, Aqua
- Singlemode 12-fiber/24-fiber/144-fiber, Plenum, Yellow



Instructions

Choose your configuration, add length and quantities. Complete the MIDs in Column "A"

Quick-Turn Product Listing

Fully Configured MID	Description	C	D	E
A	B			
Jumpers (duplex LC-LC)		LEN	UOM	Qty
FEXLCLC42-MX_ ___	LazrSPEED® 550 LC to LC, Fiber Patch Cord, 1.6 mm Duplex, Riser, Aqua			
FDXLCLC42-MX_ ___	LazrSPEED® 550 LC to LC, Fiber Patch Cord, 1.6 mm Duplex, Plenum, Aqua			
FEWLCLC42-JX_ ___	TeraSPEED® LC to LC, Fiber Patch Cord, 1.6 mm Duplex, Riser, Yellow			
InstaPATCH® 360 Array Patchcords (unpinned MPO-unpinned MPO), Plenum		LEN	M or F	Qty
FQXMPMPGD-MA_ ___	LazrSPEED® 550 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FQZMPMPGD-MA_ ___	LazrSPEED® 300 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
InstaPATCH® 360 Array Patchcords (unpinned MPO-pinned MPO), Plenum		LEN	M or F	Qty
FQXMPMXGD-MA_ ___	LazrSPEED® 550 MPO (female) to MPO (male), 12-Fiber, Plenum, Aqua			
FQZMPMXGD-MA_ ___	LazrSPEED® 300 MPO (female) to MPO (male), 12-Fiber, Plenum, Aqua			
InstaPATCH® 360 QSFP Arrays (unpinned MPO-8LC), Plenum		LEN	M or F	Qty
FQXQPLCG8-MD_ ___	LazrSPEED® 550 MPO (female) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=12"			
FQXQPLCG8-ME_ ___	LazrSPEED® 550 MPO (female) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=24"			
FQXQPLCG8-MH_ ___	LazrSPEED® 550 MPO (female) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=48"			
InstaPATCH® 360 QSFP Arrays (pinned MPO-8LC), Plenum		LEN	M or F	Qty
FQXQLCG8-MD_ ___	LazrSPEED® 550 MPO (male) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=12"			
FQXQLCG8-ME_ ___	LazrSPEED® 550 MPO (male) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=24"			
FQXQLCG8-MH_ ___	LazrSPEED® 550 MPO (male) to LC, QSFP Array Cord, 8-Fiber, Plenum, Aqua, BO=48"			
InstaPATCH® 360 Array Fanout (unpinned MPO-12LC), Plenum		LEN	M or F	Qty
FQXMPLCGD-MD_ ___	LazrSPEED® 550 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=12"			
FQXMPLCGD-ME_ ___	LazrSPEED® 550 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=24"			
FQXMPLCGD-MH_ ___	LazrSPEED® 550 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=48"			
FQZMPLCGD-MD_ ___	LazrSPEED® 300 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=12"			
FQZMPLCGD-ME_ ___	LazrSPEED® 300 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=24"			
FQZMPLCGD-MH_ ___	LazrSPEED® 300 MPO (female) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=48"			
InstaPATCH® 360 Array Fanout (pinned MPO-12LC), Plenum		LEN	M or F	Qty
FQXMXLCGD-MD_ ___	LazrSPEED® 550 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=12"			
FQXMXLCGD-ME_ ___	LazrSPEED® 550 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=24"			
FQXMXLCGD-MH_ ___	LazrSPEED® 550 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=48"			
FQZMXLCGD-MD_ ___	LazrSPEED® 300 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=12"			
FQZMXLCGD-ME_ ___	LazrSPEED® 300 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=24"			
FQZMXLCGD-MH_ ___	LazrSPEED® 300 MPO (male) to LC, Array Fanout, 12-Fiber, Plenum, Aqua, BO=48"			

Quick-Turn Product Listing (Continued)

Fully Configured MID	Description	C	D	E
A	B	LEN	M or F	Qty
InstaPATCH® 360 Pre-terminated Trunk Cable, Plenum with Gland Option		LEN	M or F	Qty
FGXMPMPAD-MB_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGXMPMPAF-MB_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGXMPMPAH-MB_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 48-Fiber, Plenum, Aqua			
FGXMPMPAL-MB_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 96-Fiber, Plenum, Aqua			
FGXMPMPAM-MB_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 144-Fiber, Plenum, Aqua			
FGZMPMPAD-MB_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGZMPMPAF-MB_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGWMPMPAD-JB_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 12-Fiber, Plenum, Yellow			
FGWMPMPAF-JB_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 24-Fiber, Plenum, Yellow			
FGWMPMPAM-JB_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 144-Fiber, Plenum, Yellow			
InstaPATCH® 360 Pre-terminated Trunk Cable, Plenum without Gland Option		LEN	M or F	Qty
FGXMPMPAD-MA_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGXMPMPAF-MA_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGXMPMPAH-MA_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 48-Fiber, Plenum, Aqua			
FGXMPMPAL-MA_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 96-Fiber, Plenum, Aqua			
FGXMPMPAM-MA_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 144-Fiber, Plenum, Aqua			
FGZMPMPAD-MA_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGZMPMPAF-MA_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGWMPMPAD-JA_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 12-Fiber, Plenum, Yellow			
FGWMPMPAF-JA_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 24-Fiber, Plenum, Yellow			
FGWMPMPAM-JA_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 144-Fiber, Plenum, Yellow			
InstaPATCH® 360 Pre-terminated Trunk Cable, Plenum with Gland Option AND Pulling Grip		LEN	M or F	Qty
FGXMPMPAD-MC_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGXMPMPAF-MC_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGXMPMPAH-MC_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 48-Fiber, Plenum, Aqua			
FGXMPMPAL-MC_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 96-Fiber, Plenum, Aqua			
FGXMPMPAM-MC_ _ _ _	LazrSPEED® 550 MPO (female) to MPO (female), 144-Fiber, Plenum, Aqua			
FGZMPMPAD-MC_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 12-Fiber, Plenum, Aqua			
FGZMPMPAF-MC_ _ _ _	LazrSPEED® 300 MPO (female) to MPO (female), 24-Fiber, Plenum, Aqua			
FGWMPMPAD-JC_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 12-Fiber, Plenum, Yellow			
FGWMPMPAF-JC_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 24-Fiber, Plenum, Yellow			
FGWMPMPAM-JC_ _ _ _	TeraSPEED® MPO (female) to MPO (female), 144-Fiber, Plenum, Yellow			

Shipping

- The customer pays shipping charges.
- Clear shipping instructions, including: ship to address, shipping options, and account number (FedEx, UPS. Etc.), must be included in the purchase order.

Additional Shipping Logistics

- Suggestion for Customer carrier request questions: (US ship from to US destination)
 - FedEx Small Parcel – requires carrier account (9 digit #), is it a recipient or third party account and service level of one of each of the following service levels: Priority Overnight, Standard Overnight, FedEx 2 day, FedEx Express Saver.
 - FedEx Air Freight – on larger orders, ask up front if customer has a weight limit or limit of quantity of cartons before requiring palletization. If shipment requires air freight service, request carrier, valid air freight account (9 digit #), is it a recipient or third party account, and one of the following service levels: FedEx 1 Day Air Freight, FedEx 2 Day Air Freight, FedEx 3 Day Air Freight.
 - UPS (Brown) Small parcel - require carrier account (6 digit, usually alpha numeric), is it a recipient or third party account, bill to zip code for third party account (sometimes required for UPS to create label if consignee zip is different than bill to account zip) and service level of one of each of the following service levels: UPS Next Day Air, UPS 2nd day Air, UPS 3 Day Select.
 - UPS Supply Chain Solutions (UPS Air Freight division) - require carrier account (9 digit), bill to zip code for account (sometimes required for UPS to create label if consignee zip is different than bill to account zip) and service level of one of each of the following service levels: UPS Next Day Air Freight, UPS 2nd Day Air Freight, UPS 3 Day Air Freight.

Packaging Guidance

	Carton	Spool	Wooded reel	Weight 1000 Ft
12f	<=130 Ft	131-999 Ft	>1000 Ft	20 Lbs
24f	<=100 Ft	101-999 Ft	>1000 Ft	25 Lbs
48f	<=100 Ft	101-999 Ft	>1000 Ft	60 Lbs
96f	<=100 Ft	085-500 Ft	> 500 Ft	60 Lbs @ 501Ft
144f	<= 65 Ft	066-265 Ft	> 266 Ft	60 Lbs @ 266Ft

- The guide on length limits will keep the size of packaging required to hold product within a small parcel transportation category. If customer orders various lengths, customer may receive multiple small cartons. This is a packaging question based upon vendor capability.
- Black spool dimensions are: 15in. X 9.25 in. X 15in.
- Small wooden reel dimensions are: 24.75 in. X 12.25 in. X 24.75 in.
- Black Plastic Spool or Small Wooden reel ****310 Wooden reel**** increment length limit before Air Freight is required
- 310 wooden reel cannot be shipped small parcel. It would be required to be placed on a pallet and AIR FREIGHT division information would be required from customer at time SO is placed.

For ordering information or questions contact your local sales and support representatives.