

High Capacity Cage Mount Monopole Platform: New Product

Announcing the release of a new family of high capacity monopole platforms designed for the demands of both today's and future 5G loading requirements. The MC-CG Series features a cage mount design that provides 24" of working space* under the antenna while providing a work platform for installers. It is designed for monopoles ranging from 12" to 50" and can hold up to 5 antenna pipes per sector. Three different models are available that are AT&T approved and rated to Heavy 5, Heavy 10, WLL, and FirstNET antenna mount specifications. The MC-CG also features a separate equipment rig point rated for 3,600 pounds for added installer convenience.

- High Capacity Cage Mount Platform
- Designed for 12" to 50" Monopoles
- Provides 24" of working area below antennas*
- Includes 3,600 lb rated Equipment Rig Point
- Base Kits with Pipe Mounts (Pipes ordered separately)



* with standard 8-foot antennas

Ordering Information:

Part Number	Description – for 12" to 50" Monopoles	Mount Rating	AT&T CEQ Number
MC-CGA10M-B	MC-CGA Platform; 10.5ft face; (12) pipe mounts; No Antenna Pipes	Heavy 5	ANT.16867
MC-CGA12M-B	MC-CGA Platform; 12.5ft face; (12) pipe mounts; No Antenna Pipes	Heavy 5	ANT.16868
MC-CGB10M-B	MC-CGB Platform; 10.5ft face; (12) pipe mounts; No Antenna Pipes	Heavy 10	ANT.16869
MC-CGB12M-B	MC-CGB Platform; 12.5ft face; (12) pipe mounts; No Antenna Pipes	Heavy 10	ANT.16870
MC-CGC12M-B	MC-CGC Platform; 12.5ft face; (12) pipe mounts; No Antenna Pipes	WLL/FirstNET	ANT.16871
MT-651-120	Antenna Pipe 2-3/8in x 120in; For Heavy 5 & Heavy 10 Platforms	Heavy 5/ 10	ANT.16872
MT546120120	Antenna Pipe; 2-7/8in x 120in; For WLL & FirstNET Platforms	WLL/FirstNET	Pending

Supporting Information

Please contact your local CommScope representative or steelproducts@commscope.com for more information.