

Class B2ca SYSTIMAX InstaPATCH Cu: New Product

Europe

CommScope is proud to announce the release and availability of the SYSTIMAX family of InstaPATCH Cu assemblies to satisfy the Construction Products Regulation (CPR) requirements of the European Union Member States.

The SYSTIMAX Class B2ca InstaPATCH assemblies utilize SYSTIMAX Class B2ca cables which are approved by authorized Notified Bodies. The Declaration of Performance (DoP) document for each cable is easily accessible via our online electronic catalog.

The SYSTIMAX Class B2ca InstaPATCH Cu come in three (3) families – Category 6/Class E Unshielded, Category 6A/Class Ea Unshielded and Category 6A/Class Ea Shielded. Each of these three families are available in either 6- or 24-port assemblies using either sleeving or hook-n-loop options. Additionally, the interface orientation is available in all the applicable orientations for that interface. For available interface orientations and information outlet and cable jacket colors referred to the E-Catalog. To decrease lead-times and improve availability CommScope has satisfied both Class Cca and B2ca requirements with the higher safety rated Class B2ca Zone Extension Cords.



- EN50575 CPR Cable EuroClass: B2ca | s1 | d0 | a1
- Utilizes solid conductor, horizontal cables to support zone extension applications
- Supports IEEE 802.3af, 802.3at and proposed 802.3bt POE applications
- GigaSPEED X10D® supports ANSI/TIA 568-C.2 Category 6A / ISO 11801 Class EA Patch Cord Performance
- GigaSPEED XL® supports ANSI/TIA 568-C.2 Category 6/ ISO 11801 Class E Patch Cord Performance
- Supports SYSTIMAX Channel and Application warranties.
- Available to order from January 1, 2019

SYSTIMAX B2ca InstaPATCH Cu Assemblies:

Base Code	Description	Information Outlet Color	Cable Jacket Color (s)	Model Number
Category 6/Class E U/UTP, Class B2ca, InstaPATCH Cu				
CRRXB	InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to Unterminated, 6 links	0=NA	8=White Z=Blue	IP06-06BUTP-1100E-BLUNT
CRRRB	InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 6 links	0=NA	8=White Z=Blue	IP06-06BUTP-1100E-1100E
CRRXG	InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to unterminated, 24 links	0=NA	8=White Z=Blue	IP06-24BUTP-1100E-BLUNT
CRRRG	InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 24 links	0=NA	8=White Z=Blue	IP06-24BUTP-1100E-1100E
Category 6A/Class Ea, Class B2ca U/UTP, InstaPATCH Cu				
CSRRB	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 6 links	0=NA	8=White	IP6A-06BUTP-1100E-1100E
CSGRB	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, RJ45 to 360 1100 Evolve module, 6 links	0=NA	8=White	IP6A-06BUTP-PG1S-1100E
CSAAB	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 6 links	8=White	8=White	IP6A-06BUTP-O1S-O1S
CSRRG	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 24 links	0=NA	8=White	IP6A-24BUTP-1100E-1100E
CSHRG	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, dual row standard density RJ45 plug to 360 1100 Evolve module, 24 links	0=NA	8=White	IP6A-24BUTP-PG2S-1100E
CSAAG	InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 24 links	8=White	8=White	IP6A-24BUTP-O1S-O1S

Category 6A/Class Ea, Class B2ca F/FTP, InstaPATCH Cu				
CTAAB	InstaPATCH® Cu GigaSPEED X10D® F/FTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 6 links	1=Black	8=White	IP6A-06BFTP-O1S-O1S
CTAJB	InstaPATCH® Cu GigaSPEED X10D® F/FTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to dual row high density RJ45 plug, 6 links	1=Black	8=White	IP6A-06BFTP-O1S-PG2H
CTAAG	InstaPATCH® Cu GigaSPEED X10D® F/FTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to single row standard density outlet, 24 links	1=Black	8=White	IP6A-24BFTP-O1S-O1S
CTAGG	InstaPATCH® Cu GigaSPEED X10D® F/FTP LSZH Class B2ca Preterminated Copper Cable, single row standard density outlet to single row standard density RJ45 plug, 24 links	1=Black	8=White	IP6A-24BFTP-O1S-PG1S

Unit of Measure is Metric (M) or Imperial (F) in 1 meter or 1-foot increments.
 Lengths available from 1 meter/3 feet to 100 meter/300 feet.

Ordering Information and Data Sheets:

Please visit internal E-Catalog at <https://www.commscope.com/> and search on the desired base code.

Supporting Documents:

Please contact your local CommScope representative for additional information.