

## InstaPATCH® QUATTRO 4-port Module



### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	InstaPATCH® QUATTRO
<b>Product Type</b>	Copper cassette
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Dimensions

<b>Depth</b>	76.20 mm   3.00 in
<b>Height</b>	19.05 mm   0.75 in
<b>Width</b>	70.10 mm   2.76 in

### Electrical Specifications

<b>ANSI/TIA Category</b>	6   6A
--------------------------	--------

### Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

### General Specifications

<b>Cable Type</b>	F/UTP (shielded)   U/UTP (unshielded)
<b>Includes</b>	Label sheet
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	RJ45 jack
<b>Interface, rear</b>	MC Female connector
<b>Label Height</b>	0.16 in
<b>Label Length</b>	2.54 in
<b>Modules, quantity</b>	1
<b>Package Quantity</b>	1
<b>Total Ports, quantity, front</b>	4
<b>Total Ports, quantity, rear</b>	1

## Mechanical Specifications

**Contact Plating Material**     Precious metals  
**Material Type**                 Polycarbonate | Steel | Zinc  
**Termination Contact Plating** Precious metals

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

