



## GigaSPEED X10D® VisiPatch® 360 12U Patch Panel Kit

### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	VisiPatch®
<b>Product Type</b>	Back mount frame kit
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Dimensions

<b>Depth</b>	287.02 mm   11.30 in
<b>Height</b>	538.48 mm   21.20 in
<b>Width</b>	215.90 mm   8.50 in

### Electrical Specifications

<b>ANSI/TIA Category</b>	6A
--------------------------	----

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	Austel   CE   cUL   UL

### General Specifications

<b>Product Design</b>	VisiPatch® 360
<b>Includes</b>	Back panel   Ninety-six connecting blocks   Twelve label holders   Twelve white labels   Twelve wiring block covers   Twelve wiring blocks
<b>Package Quantity</b>	1

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

