



360G2 Cassette 6 SC Singlemode Blue with Pigtails B

Product Classification

Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	6

Dimensions

Depth	119.38 mm 4.70 in
Height	30.48 mm 1.20 in
Pigtail Length	1.5 m 4.9 ft
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	SC
Adapter Color	Blue
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	6

Optical Performance

Insertion Loss, typical	0.40 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860240738 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, red, 1.5 m

- 760095653 | X-TB-8W-RD-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode

860240746 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, black, 1.5 m

- 760095661 | X-TB-8W-BK-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode

860240753 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, yellow, 1.5 m

- 760038570 | X-TB-8W-YL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
- 760200568 | X-TB-8G-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860240761 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, violet, 1.5 m

- 760095679 | X-TB-8W-VI-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode

860240779 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, rose, 1.5 m

- 760095687 | X-TB-8W-RS-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode

860240787 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, aqua, 1.5 m

- 760095695 | X-TB-8W-AQ-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode

760049783 | SFA-SC06-BL-SHUTTERED — TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack