

Split Shingle for Wall Mount Building Entrance, 2 port, 0.708 in

Product Classification

Portfolio	Uniprise®
Product Type	Shingle
Regional Availability	North America

Construction Materials

Material Type	Steel
----------------------	-------

Dimensions

Depth	6.35 mm 0.25 in
Height	76.20 mm 3.00 in
Width	203.20 mm 8.00 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Application	Accepts cable with 0.24–0.708 in OD
Color	Gray
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

