

ProPatch® Integrated Standard Size Video Panel, 2 RU, 3 x 26

Product Classification

Brand	Pro Patch®
Product Series	ProPatch
Product Type	Video patch panel
Regional Availability	EMEA Latin America North America

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

Characteristic Impedance	75 ohm
---------------------------------	--------

Environmental Specifications

Environmental Standard	MIL-STD-202
Flammability Rating	UL 94 V-0
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)

General Specifications

Total Ports, quantity	78
Application	For use with WECO HD standard size video patch cords
Color	Black
Growth Configuration	Fully loaded
Includes	Designation strips
Interface, front	SVJ-2 jack
Interface, rear	BNC female adapter
Mount Type	Rack, horizontally oriented
Rack Type	EIA 19 in
Rack Units	2.0

Mechanical Specifications

Finish	Powder coated
Material Type	Steel
Plug Insertion Force, maximum	12 N

Plug Insertion Life, minimum 20000 times

Plug Retention Force, minimum 3 N | 1 lbf

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

