



MRJ21™ XG Flush Mount Patch Panel, 48 RJ45 ports, 12 MRJ21™ plugs, straight, 1 RU for 10 GbE, black

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	MRJ21™
<b>Product Series</b>	MRJ21
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Australia/New Zealand   EMEA

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6A
<b>Transmission Standard</b>	ANSI/TIA-568-C.2   ISO/IEC 11801 Class EA

## General Specifications

<b>Total Ports, quantity</b>	48
<b>Color</b>	Black
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	RJ45 jack
<b>Interface, rear</b>	MRJ21 connector
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Box
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1.0

## Mechanical Specifications

<b>Panel Style</b>	Straight
<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Steel
<b>Panel Mounting</b>	Flush

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

