



SYSTIMAX 360™ iPatch® Evolve High Density F/UTP Angled Modular Panel, 48 port

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	266.70 mm 10.50 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	88.90 mm 3.50 in
Weight	2.72 kg 6.00 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE ETL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	48
Cable Type	Shielded

Color	Cool gray
Includes	Cable management bar Four #12-24 dog point mounting screws Instruction sheet Modular jacks (48) Panel Two #12 washers Two #12-24 screws
Package Quantity	1
Rack Units	2.0

Mechanical Specifications

Panel Style	Angled
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

