



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 48 Port, 5 pack

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	iPatch®   SYSTIMAX 360™
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in
<b>Diameter Over Dielectric, minimum</b>	0.762 mm   0.030 in
<b>Weight</b>	0.11 kg   0.25 lb

## Electrical Specifications

<b>ANSI/TIA Category</b>	6   6A
<b>Current Rating at Temperature</b>	1.5 A @ 20 °C   1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1,500 Vac @ 60 Hz
<b>Dielectric Withstand Voltage, RMS, contact-to-contact</b>	1,000 Vac @ 60 Hz

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	ACMA   CE   cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Intelligence Type</b>	iPatch® upgrade kit
<b>Total Ports, quantity</b>	48
<b>Color</b>	Cool gray
<b>Package Quantity</b>	5

## Mechanical Specifications

<b>Panel Style</b>	Angled
<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

