



Fiber Optic Termination Panel, fixed tray, 1 RU, 19 in, unloaded, 12/24-port, black

Product Classification

Product Type	Fiber patch panel
Regional Availability	Australia/New Zealand

Dimensions

Depth	295.00 mm 11.61 in
Height	44.45 mm 1.75 in
Width	375.00 mm 14.76 in
Weight	6.40 kg 14.11 lb

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)

General Specifications

Rack Units	1.0
Body Style	Symmetrical
Color	Black
Color, front	Black
Growth Configuration	Unloaded
Includes	Mounting hardware
Package Quantity	1
Rack Type	EIA 19 in
Total Ports, quantity	24
Transmission Standards	AS/NZS 2211.1 IEC 60852-1

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

