

## MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Splice Cassette, 24 LC, aqua

### Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Brand</b>	MPOptimate®
<b>Product Series</b>	UCP
<b>Product Type</b>	Fiber cassette
<b>Regional Availability</b>	Australia/New Zealand   EMEA

### Construction Materials

<b>Fiber Type</b>	OM3
<b>Fiber Mode</b>	Multimode
<b>Total Fibers, quantity</b>	24

### Environmental Specifications

<b>Operating Temperature</b>	0 °C to +70 °C (+32 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

<b>Interface, front</b>	LC
<b>Adapter Color</b>	Aqua
<b>Adapters, quantity, front</b>	6
<b>Application</b>	For use with Universal Connectivity Product (UCP) panels
<b>Body Style</b>	Quad
<b>Color, front</b>	Black
<b>Color, housing</b>	Black
<b>Interface Feature, front</b>	Standard
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Total Ports, quantity, front</b>	24

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

