



RJ45 Patch Panel, SL Series, S/STP, 24-port, gray, unloaded

Product Classification

Portfolio	CommScope®
Product Series	SL Series
Product Type	RJ45 patch panel
Regional Availability	EMEA

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Environmental Specifications

Operating Temperature -25 °C to +50 °C (-13 °F to +122 °F)

General Specifications

Total Ports, quantity	24
Cable Type	Shielded
Application	For use with SL Series outlets
Color	Gray
Growth Configuration	Unloaded
Interface, front	RJ45 jack
Package Quantity	1
Packaging Type	Bag Box
Rack Type	EIA 19 in
Rack Units	1.0

Mechanical Specifications

Panel Style	Straight
Material Type	High-impact, flame retardant, thermoplastic Steel
Panel Mounting	Flush
Termination Type	IDC

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

