

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Splice Cassette, 24 LC/APC, green

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Series	UCP
Product Type	Fiber cassette
Regional Availability	Australia/New Zealand EMEA

Construction Materials

Fiber Type	OS2
Fiber Mode	Singlemode
Total Fibers, quantity	24

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Interface, front	LC
Adapter Color	Green
Adapters, quantity, front	6
Application	For use with Universal Connectivity Product (UCP) panels
Body Style	Quad
Color, front	Black
Color, housing	Black
Interface Feature, front	APC
Package Quantity	1
Packaging Type	Bag Carton
Total Ports, quantity, front	24

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

