

Fiber adapter plate, 1U, unpopulated, for holding up to 4 Quick-Fit modules

Product Classification

| | |
|------------------------------|------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Fiber adapter plate |
| Regional Availability | Australia/New Zealand EMEA |

Dimensions

| | |
|---------------|----------------------|
| Depth | 39.70 mm 1.56 in |
| Height | 44.45 mm 1.75 in |
| Width | 482.60 mm 19.00 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Environmental Space | Indoor |
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Relative Humidity | 5%–95%, non-condensing |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|-------------------------|--------------|
| Color | Black |
| Package Quantity | 1 |
| Packaging Type | Bag Carton |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

