



Fiber Optic Patch Cord, singlemode, SC/PC-SC/PC, duplex, 2.5 mm tight cable, LSZH, 1 m, yellow

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	2
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	1.00 m 3.28 ft
Diameter Over Jacket	2.50 mm 0.10 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	SC/UPC
Interface, connector B	SC/UPC
Color, boot A	Red
Color, boot B	Black
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1

Optical Performance

Insertion Loss, maximum, connector A	0.30 dB
---	---------

6348260-1

Insertion Loss, maximum, connector B 0.30 dB

Return Loss, minimum, connector A 45.00 dB

Return Loss, minimum, connector B 45.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

