



Highband® RJ45 Patch Cord, category 6, bag of 2, blue, 2.1 m

## Product Classification

<b>Brand</b>	Highband®
<b>Product Series</b>	Highband
<b>Product Type</b>	Twisted pair patch cord
<b>Regional Availability</b>	Australia/New Zealand   EMEA

## Dimensions

<b>Cord Length</b>	2.10 m   6.89 ft
<b>Diameter Over Jacket</b>	5.40 mm   0.21 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6
<b>Insulation Resistance, minimum</b>	100 mOhm

## Environmental Specifications

<b>Flammability Rating</b>	UL 444
<b>Operating Temperature</b>	-10 °C to +75 °C (14 °F to +167 °F)
<b>Relative Humidity</b>	Up to 93%, non-condensing

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Interface, connector A</b>	RJ45 plug
<b>Interface, connector B</b>	RJ45 plug
<b>Jacket Color</b>	Blue
<b>Package Quantity</b>	2
<b>Pairs, quantity</b>	4

## Mechanical Specifications

<b>Conductor Type</b>	Stranded
<b>Conductor Gauge, stranded</b>	24 AWG

**Wiring**

T568B

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

