

BK4VXM-LCP-LCP



ProPatch® Mini LCP High-Performance Patch Cords, 4 ft

Product Classification

Brand	Pro Patch®
Product Series	ProPatch
Product Type	RF cable assembly
Regional Availability	EMEA Latin America North America

Dimensions

Cord Length	1.22 m 4.00 ft
--------------------	------------------

Electrical Specifications

Data Rate, Supported	Uncompressed HDTV signals (1.485 Gbit/s)
Impedance	75 ohm
Safety Voltage Rating	600 V

Environmental Specifications

Environmental Space	Indoor
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)

General Specifications

Cable Type	240 Series
Interface, connector A	LCC plug
Interface, connector B	LCC plug
Jacket Color	Black
Application	For use with LCC video panels
Interface Feature, connector A	Booted
Interface Feature, connector B	Booted

Mechanical Specifications

Conductor Material	Beryllium copper
Contact Plating Material	Gold

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

