



Copper Patch Cord, 2P AMP TWIST to RJ45, S/FTP, LZSH, stranded, white, 2 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	2.00 m 6.56 ft
Diameter Over Jacket	5.59 mm 0.22 in

Electrical Specifications

ANSI/TIA Category	5e
--------------------------	----

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	2P AMP-TWIST plug
Jacket Color	White
Pairs, quantity	2

Mechanical Specifications

Conductor Type	Stranded
-----------------------	----------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
RCM	Compliant to electrical safety, EMC, EME & telecommunications requirements

