

MRJ21™ High Speed Cable Assembly, MRJ21-6xRJ45, 180° back shell, 1GbE, 24-pair, U/F/UTP, 10 m

- Universal modular copper cabling platform for applications such as Gigabit Ethernet, VoIP and Power over Ethernet
- Increased I/O port density and cleaner cabling schemes compared to RJ45 connectors and cabling
- Robust die cast cable covers provide straight, or 45 deg left/right cable exit for ease of routing

Product Classification

Portfolio	CommScope®
Brand	MRJ21™
Product Series	MRJ21
Product Type	Copper trunk cable assembly
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	15.60 mm 0.61 in

Electrical Specifications

ANSI/TIA Category	6
Safety Voltage Rating	150 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Construction Type	Stranded
Interface, connector A	MRJ21 plug
Interface, connector B	RJ45 plug
Application	Ethernet, 1 GbE
Cable Type	F/UTP (shielded)
Interface Feature, connector A	Backshell, 180°
Interface Feature, connector B	Booted
Jacket Color	White
Package Quantity	1
Pairs, quantity	24
Total Ports, quantity	6

Mechanical Specifications

1-1711789-0

Conductor Gauge, solid	24 AWG
Conductor Material	Bare copper
Conductor Type	Solid

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

