



Fiber Optic Patch Cord, Duplex, Singlemode, LC/UPC to SC/UPC, yellow, 1 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia EMEA Latin America North America

Construction Materials

Fiber Type	OS2
Total Fibers, quantity	2
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	1.00 m 3.28 ft
Diameter Over Jacket	1.80 mm 0.07 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	LC/UPC
Interface, connector B	SC/UPC
Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs, flipped

Optical Performance

Insertion Loss, maximum, connector A 0.30 dB

Insertion Loss, maximum, connector B 0.30 dB

Return Loss, minimum, connector A 45.00 dB

Return Loss, minimum, connector B 45.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

