

RJ45 Consolidation Point, category 6A, F/FTP, white, 4 m



## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Portfolio</b>             | NETCONNECT®                         |
| <b>Product Type</b>          | Twisted pair patch cord             |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA |

## Dimensions

|                    |                   |
|--------------------|-------------------|
| <b>Cord Length</b> | 4.00 m   13.12 ft |
|--------------------|-------------------|

## Electrical Specifications

|                          |    |
|--------------------------|----|
| <b>ANSI/TIA Category</b> | 6A |
|--------------------------|----|

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

## General Specifications

|                               |                  |
|-------------------------------|------------------|
| <b>Cable Type</b>             | F/UTP (shielded) |
| <b>Interface, connector A</b> | RJ45 plug        |
| <b>Interface, connector B</b> | AMP-TWIST jack   |
| <b>Jacket Color</b>           | White            |
| <b>Package Quantity</b>       | 1                |
| <b>Pairs, quantity</b>        | 4                |

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

