



Horizontal Copper Cable, category 6, 4 pair, UTP, PVC, 24 AWG, 305 m reel-in-box, white

OBSOLETE

This product was discontinued on: September 30, 2019

Replaced By

1427071-2
CS30CM WHT C6 4/24 U/UTP RIB 305M Copper Cable, category 6, 4 pair, UTP, CM rated, 24 AWG, 305 m reel in box, white

Product Classification

Portfolio NETCONNECT®
Product Type Twisted pair cable
Regional Availability EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass Eca

Construction Materials

Jacket Material PVC
Conductor Material Bare copper
Insulation Material Polyolefin

Dimensions

Cable Length 305 m | 1000 ft
Diameter Over Jacket, nominal 5.700 mm | 0.224 in

Electrical Specifications

ANSI/TIA Category 6
Operating Voltage, maximum 80 V
Transmission Standards ANSI/TIA-568-C.2 | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class E

General Specifications

Cable Type U/UTP (unshielded)

Packaging Type	Reel in box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU CENELEC	Compliant EN 50575 compliant, Declaration of Performance (DoP) available

