

Outdoor Fiber Cable, 96-fiber, singlemode OS2, loose tube, blue

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber OSP cable
<b>Regional Availability</b>	Australia/New Zealand

## Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492CAAB (OS2)
-----------------------------	-------------------

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled

## Construction Materials

<b>Jacket Material</b>	Nylon
<b>Total Fiber Count</b>	96
<b>Fiber Type</b>	OS2
<b>Fibers per Subunit, quantity</b>	6
<b>Jacket Color</b>	Blue

## Dimensions

<b>Diameter Over Jacket</b>	8.90 mm   0.35 in
-----------------------------	-------------------

## Environmental Specifications

<b>Environmental Space</b>	Buried
<b>Operating Temperature</b>	-10 °C to +70 °C (+14 °F to +158 °F)

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant



\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable