

Indoor/Outdoor Fiber Optic Cable, 6-fiber, loose tube, LSZH, SM, 1000 m

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Regional Availability</b>	Asia

## Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492CAAB (OS2)
-----------------------------	-------------------

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled

## Construction Materials

<b>Total Fiber Count</b>	6
<b>Fiber Type</b>	OS2
<b>Fibers per Subunit, quantity</b>	6
<b>Jacket Color</b>	Black

## Dimensions

<b>Cable Length</b>	1000 m   3281 ft
<b>Cable Weight</b>	73.0 kg/km
<b>Diameter Over Jacket</b>	8.00 mm   0.31 in

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	160.0 mm   6.3 in
<b>Minimum Bend Radius, unloaded</b>	80.0 mm   3.1 in
<b>Tensile Load, long term, maximum</b>	800 N   180 lbf
<b>Tensile Load, short term, maximum</b>	1800 N   405 lbf

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Installation Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable