

Fiber Optic Cable, 4-fiber, OM3, 2000 m, aqua

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Dca   s2   d2   a1
------------------------------------	--------------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	1.00 dB/km @ 1300 nm 3.50 dB/km @ 850 nm
<b>Standards Compliance</b>	TIA-492AAAC (OM3)

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-free

## Construction Materials

<b>Total Fiber Count</b>	4
<b>Fiber Type</b>	OM3
<b>Fibers per Subunit, quantity</b>	4
<b>Jacket Color</b>	Aqua

## Dimensions

<b>Cable Length</b>	2000 m   6562 ft
<b>Cable Weight</b>	47.0 kg/km
<b>Diameter Over Jacket</b>	6.40 mm   0.25 in

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	140.0 mm   5.5 in
<b>Minimum Bend Radius, unloaded</b>	129.8 mm   5.1 in
<b>Tensile Load, long term, maximum</b>	650 N   146 lbf
<b>Tensile Load, short term, maximum</b>	1250 N   281 lbf

## Environmental Specifications

**Environmental Space** Universal Low Smoke Zero Halogen (ULSZH)  
**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU CENELEC	Compliant EN 50575 compliant, Declaration of Performance (DoP) available



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable