



Horizontal Copper Cable, category 6, 4 pair, UTP, PVC, 24 AWG, 500 m wooden reel, white

## **OBSOLETE**

**This product was discontinued on: September 30, 2019**

### **Replaced By**

1427071-2  
CS30CM WHT C6 4/24 U/UTP RIB 305M Copper Cable, category 6, 4 pair, UTP, CM rated, 24 AWG, 305 m reel in box, white

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable
<b>Regional Availability</b>	Australia/New Zealand   EMEA

## Standards And Qualifications

EN50575 CPR Cable EuroClass Eca

## Construction Materials

<b>Jacket Material</b>	PVC
<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin

## Dimensions

<b>Cable Length</b>	500 m   1640 ft
<b>Diameter Over Jacket, nominal</b>	5.700 mm   0.224 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6
<b>Operating Voltage, maximum</b>	80 V
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
-------------------	--------------------

<b>Packaging Type</b>	Reel
<b>Pairs, quantity</b>	4
<b>Cable Component Type</b>	Horizontal
<b>Jacket Color</b>	White
<b>Conductor Gauge, singles</b>	24 AWG
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU CENELEC	Compliant EN 50575 compliant, Declaration of Performance (DoP) available

